# Low voltage and cos-phi monitoring

### AD-LW 100 GS

#### Description

The AD-LW 100 GS monitors the load condition of inductive consumers. The main application areas are asynchronous motors with a 1 or 3 phase mains, whose load changes considerably. An evaluation of the cos-phi max value is carried out and simultaneously an independent under voltage monitoring. Exceeding the set limit values releases a contact. The switching conditions are displayed at the front via LEDs

#### Application

Function the measuring principle for the cos-phi is based on the evaluation of the phase shift between voltage and current in a




phase. The actual measuring size is therefore the phase angel between voltage and current. The setting value of the cos-phi or the phase angle is therefore only correct for sinusoidal sizes. The phase shift runs almost in reverse to the load. A cos-phi of 0 (= 90°) is therefore equivalent to a low load whereas a cos-phi of 1 (=  $0^{\circ}$ ) is equivalent to a high load.)


#### Specification

type	1 channel housing: AD-LW 100 GS	
power supply	ALLPOWER 20253V AC/DC internal electrically insulated	
power consumption	approx. 2,5 VA resp. 4 W	
input voltage	3 x 180240 VAC L1 / L2 / L3 against neutral wire	
input current	1 x 15 A	
	current in L1	
adjustment range	with trimmer on the front side (270°) cos-phi: 0,20,9 voltage: 180250 VAC	
output	each one normally open contact with switch function on front side	
hysteresis	approx. 3% from range	
accuracy	approx. 2%	
insulation test voltage	input/output signal/power supply	5 kV RMS 4 kV RMS
CE-conformity	EN 50081-2, EN 50082-2	
ambient temperature	0 to 50°C	
variations	cos-phi min + low pressure cos-phi min + cos-phi min	

## connection and dimension: AD-LW 100 GS Input: 3 x 180-250 V AC, 1x 0-5 A AC



connection data: fine-wire 2,5 mm<sup>2</sup> single-wire 4,0 mm<sup>2</sup> max. voltage 250 VAC manner of fastening attachment rail NS 35 / 7,5 protection IP 20 weight approx. 200 g



Printed 01/2008. We reserve the right for technical changes



Felix-Wankel-Str. 13 Tel. +49 (0)7046-875 vertrieb@ad-messtechnik.de 74374 Zaberfeld Fax +49 (0)7046-7678 www.adamczewski.com